

# Declaration of Compatibility

## SLK Hoist Slings



Welltoll Group

SLK Vertriebs GmbH  
Am Herdicksbach 18  
D-45731 Waltrop

With this declaration of compatibility, SLK Vertriebsgesellschaft mbH confirms that the slings distributed by it can be used with all mobile patient hoists listed below - active hoists/universal hoists - and overhead hoists from other manufacturers, which are equipped with a hanging system with open or closed hooks. These hooks shall be capable of accommodating a 50 mm wide sling loop and keeping it under tension. The hoist must be equipped with a 2-, 3-, 4- or 8-point Spreader bar. Systems with perforated metal or plastic eyelets are not compatible.

### Overview of combinations released by SLK

| SLK                                                                                                                                                                                                                        | Spreader Bar                                                                                                  | Sling Type        |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|-------------------|
| Carry 185 Eco, Carry 185 Classic/Classic e,<br>Carry 185 Pro/Pro e, Carry 185 Pro L/Pro L e,<br>Carry Compact,<br>Multy Universal/Universal e,<br>Blue Flyer Compact, Blue Flyer Plus,<br>Flyer Plus, Flyer XL, Flyer Maxi | 2-Point Spreader Bar,<br>4-Point Spreader Bar H,<br>4-Point Spreader Bar X,<br>4-Point Spreader Bar Compact H | A, E              |
|                                                                                                                                                                                                                            | 8-Point Spreader Bar                                                                                          | D                 |
| Multy Aktiv/Activ e, Eazy-up® fix, Eazy-up® flex,<br>Blue Wayup, Wayup, Wayup XL, Maxxiup                                                                                                                                  | Straightening lifting arm                                                                                     | B, C              |
| Easylev, Nausilev                                                                                                                                                                                                          | Straightening lifting arm                                                                                     | B                 |
| <b>Aacurat</b>                                                                                                                                                                                                             | <b>Spreader Bar</b>                                                                                           | <b>Sling Type</b> |
| Curator, Deckenlift V4, Genius Cloth Lift                                                                                                                                                                                  | 2-Point Spreader Bar                                                                                          | A                 |
| Genius Erection Lift                                                                                                                                                                                                       | Straightening lifting arm                                                                                     | B                 |
| <b>AKS</b>                                                                                                                                                                                                                 | <b>Spreader Bar</b>                                                                                           | <b>Sling Type</b> |
| foldy, mini foldy, micro foldy, foldy XL,<br>clino II, clino XL,<br>dualo Standard, mini dualo Standard, dualo Standard XL,<br>foldo, goliath                                                                              | Standard transport Spreader Bar<br>Tandem Bar                                                                 | A                 |
|                                                                                                                                                                                                                            | Horizontal transport Spreader<br>with 8-Point holder                                                          | D                 |
| dualo Aktiv, mini dualo Aktiv, dualo Aktiv XL, torneo                                                                                                                                                                      | Straightening lifting arm                                                                                     | B                 |
| torneo II, torneo compact                                                                                                                                                                                                  | Straightening lifting arm                                                                                     | C                 |
| <b>ARJOHUNTLEIGH</b>                                                                                                                                                                                                       | <b>Spreader Bar</b>                                                                                           | <b>Sling Type</b> |
| Minstrel, Tenor                                                                                                                                                                                                            | 4-Point Spreader Bar                                                                                          | A                 |
| <b>ATO Form</b>                                                                                                                                                                                                            | <b>Spreader Bar</b>                                                                                           | <b>Sling Type</b> |
| Hospilift, Hospilift mini, Hospilift XL, Hospilift Linear, Hospilift EE,<br>Hospilift mini EE, Hospilift King, Hospilift King mini,<br>Hospilift Classic, Hospilift Classic XL                                             | Carrying Handle with 2-, 3-, 4-<br>Point Holder                                                               | A                 |
| Vitalift                                                                                                                                                                                                                   | Mounting                                                                                                      | B, C              |
| <b>Beka Hospitec</b>                                                                                                                                                                                                       | <b>Spreader Bar</b>                                                                                           | <b>Sling Type</b> |
| Carlo Alu Classic 185, Carlo Alu Classic 230, Carlo Air                                                                                                                                                                    | 2-, 4-Point Loop Spreader Bar                                                                                 | A                 |
| <b>Braus</b>                                                                                                                                                                                                               | <b>Spreader Bar</b>                                                                                           | <b>Sling Type</b> |
| Patient Lift BLC 175 B/BE, Overhead lift BLC 160-320 D/DL                                                                                                                                                                  | Multi Spreader Bar                                                                                            | A                 |
| <b>Burmeier</b>                                                                                                                                                                                                            | <b>Spreader Bar</b>                                                                                           | <b>Sling Type</b> |
| Agile                                                                                                                                                                                                                      | Transport Spreader Bar                                                                                        | A                 |
| <b>DP-Med</b>                                                                                                                                                                                                              | <b>Spreader Bar</b>                                                                                           | <b>Sling Type</b> |
| ProLift A166, A222, A333, C136, P136, CP136, ProLift Transactive<br>Xtra TXE130, TXE160, TXE200, TXE270, C380, P200                                                                                                        | 2-Point Spreader Bar , 4-Point<br>Spreader Bar                                                                | A                 |
| ProLift S222                                                                                                                                                                                                               | Straightening lifting arm                                                                                     | B, C              |

|                                                                                                                                                                                                 |                                                                                                                   |                   |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------|-------------------|
| <b>Drive Medical</b>                                                                                                                                                                            | <b>Spreader Bar</b>                                                                                               | <b>Sling Type</b> |
| Samsoft 175, Hermes                                                                                                                                                                             | Sling Bars                                                                                                        | A                 |
| <b>Etac/Molift</b>                                                                                                                                                                              | <b>Spreader Bar</b>                                                                                               | <b>Sling Type</b> |
| Molift Smart 150, Molift Mover 180, Molift Mover 2015, Molift Mover 300, Molift Partner 255, Nomand 160, Nomand 205, Nomand 230, Nomand 255 (Nomand with integrated 4-point suspension)         | 2-Point Lifting Spreader Bar (all sizes)<br>4-Point Lifting Spreader Bar (all sizes)                              | A                 |
| <b>Guldmann</b>                                                                                                                                                                                 | <b>Spreader Bar</b>                                                                                               | <b>Sling Type</b> |
| GH1, GH1F, GH1Q, GHZ, GH3, GL5                                                                                                                                                                  | Suspension Spreader Bar, H-Spreader Bar, Crossbar                                                                 | A                 |
|                                                                                                                                                                                                 | Recumbent Bar Art.-Nr.: 28456, Recumbent Bar Art.-Nr.: 28466                                                      | D                 |
| GLS5                                                                                                                                                                                            | Straightening lifting arm                                                                                         | B, C              |
| <b>Handicare</b>                                                                                                                                                                                | <b>Spreader Bar</b>                                                                                               | <b>Sling Type</b> |
| Carina350EM/EE, Eva400, Eva450, Eva600EE, Vega505EE, RiseAtlas 450, RiseBasic 300M/440M, RiseAtlas 625                                                                                          | Sling Bar, (also in combination with Sling Bar spreader M), Sling Bar RFL X4                                      | A                 |
| Mini-Lift 125, Mini-Lift 160, Mini-Lift 200                                                                                                                                                     | Straightening lifting arm                                                                                         | B, C              |
| <b>Handimove</b>                                                                                                                                                                                | <b>Spreader Bar</b>                                                                                               | <b>Sling Type</b> |
| Overhead lift 2540 / 2545 with hanging hook, 2800 / 2805, HM50 Mobile lift 1630 / 1635 / 1640 / 1641, Victor 2600, wall lift 2420 / 2431, swimming pool lifter 3200, ceiling swimming pool lift | Combi, Standard, Classic 2- and 4-point Spreader Bar, flat 2-point hanging device, model 2540/2545 only with hook | A                 |
| Active lift 1620                                                                                                                                                                                | Straightening lifting arm                                                                                         | B                 |
| <b>Heymer</b>                                                                                                                                                                                   | <b>Spreader Bar</b>                                                                                               | <b>Sling Type</b> |
| Uno, Duo, Trio, Heros 300, Klemmli                                                                                                                                                              | 2-point hanging device, 4-point hanging device small/large                                                        | A                 |
| <b>Horcher</b>                                                                                                                                                                                  | <b>Spreader Bar</b>                                                                                               | <b>Sling Type</b> |
| Diana Comfort, Ceiling lift Unilift series, Ceiling lift UPL 160 / UPL 240                                                                                                                      | 4-point Swivel Spreader Bar D2000, L101-2402, C106-100, C106-101, C106-102                                        | A                 |
| Lexa Comfort - Loop                                                                                                                                                                             | 4-point seat/lying Spreader Bar, motorised adjustment, with hook mount                                            | A                 |
| <b>Hoyer</b>                                                                                                                                                                                    | <b>Spreader Bar</b>                                                                                               | <b>Sling Type</b> |
| HOVL-100, HOVL-200, HLU-3/E-O, HLU-4/E-O, HLU-3/S, HCL-3/S, HCL-7/E, HL-200, HWL-130, HLK-6, HTL-C, Overhead Lift 72005 / 72007, Pocket-lift 72020 / 72040                                      | Swivel Spreader Bar, Cross bar with 4-point suspension                                                            | A                 |
| ALH, ALH-20                                                                                                                                                                                     | Straightening lifting arm                                                                                         | B                 |
| <b>Humancare ( distribution in Germany AKS )</b>                                                                                                                                                | <b>Spreader Bar</b>                                                                                               | <b>Sling Type</b> |
| FL180, Singel 2000, Singel 2100, Singel 4100, Singel 5100, Roomer 5200, Singel 5100 Satellit, Roomer S, Altair, HeliQ                                                                           | 2-, 4-point suspension Spreader Bar                                                                               | A                 |
| <b>Invacare</b>                                                                                                                                                                                 | <b>Spreader Bar</b>                                                                                               | <b>Sling Type</b> |
| Atlante, Birdie, Birdie Compact, Birdie Plus, Birdie Evo, Birdie Evo Compact, Birdie Evo Xplus, Jasmine, Kirilos                                                                                | 2-, 4-point Spreader Bar (all sizes)                                                                              | A                 |
| Isa, Isa Compact, Isa Xplus, Reliant 350                                                                                                                                                        | Straightening lifting arm                                                                                         | B                 |
| <b>Liko</b>                                                                                                                                                                                     | <b>Spreader Bar</b>                                                                                               | <b>Sling Type</b> |
| Golvo, M 220, M 230, Uno 100, Uno 102, Uno 200, Viking XS, Viking S, Viking M, Viking L, Viking XL                                                                                              | Sling bar Mini 220, Universal Sling Bar 350/450/600/670 Twin, Universal Side Bar, Crossbar 450/670                | A                 |
| Likorall 200, Likorall 242 ES, Likorall 242 S, Likorall 243, Likorall 250, Likorall R2R, Multirall 200                                                                                          |                                                                                                                   |                   |
| Sabina, Sabina II                                                                                                                                                                               | Straightening lifting arm                                                                                         | B                 |
| <b>Meyra</b>                                                                                                                                                                                    | <b>Spreader Bar</b>                                                                                               | <b>Sling Type</b> |
| Sito Universal Lift                                                                                                                                                                             | Transport Spreader Bar                                                                                            | A                 |
| Sito Active Lift                                                                                                                                                                                | Straightening lifting arm                                                                                         | B                 |

| <b>Novacare</b>                                                                                            | <b>Spreader Bar</b>                                    | <b>Sling Type</b> |
|------------------------------------------------------------------------------------------------------------|--------------------------------------------------------|-------------------|
| Prolift A166, A222, A333, Cacero                                                                           | Single Sling Spreader Bar<br>Double Sling Spreader Bar | A                 |
| Prolift Argo                                                                                               | Straightening lifting arm                              | B                 |
| <b>Oxford</b>                                                                                              | <b>Spreader Bar</b>                                    | <b>Sling Type</b> |
| Mini 140, Midi 180, Maxi 180, Major 200, Advance, Presence, Dipper, Elara 227, Elara 284, Voyager Portable | Spreader Bar                                           | A                 |
| Standaid 140, Ascend, Elevante, Journey                                                                    | Straightening lifting arm                              | B                 |
| <b>Rebotec</b>                                                                                             | <b>Spreader Bar</b>                                    | <b>Sling Type</b> |
| Arnold 125, Arnold 150, Arnold 250                                                                         | Standard transport Spreader Bar, 4-Pointbügel          | A                 |
| James 150, James 250                                                                                       | Straightening lifting arm                              | B                 |
| <b>Sunrise</b>                                                                                             | <b>Spreader Bar</b>                                    | <b>Sling Type</b> |
| Sunlift Micro, Sunlift Mini, Sunlift Midi, Sunlift Major                                                   | Spreader Bar                                           | A                 |
| <b>Vassilli</b>                                                                                            | <b>Spreader Bar</b>                                    | <b>Sling Type</b> |
| 10.77/170, 10.77M170, 10.77N170, 10.77/200XXL                                                              | Spreader Bar                                           | A                 |
| 10.77CS-150, 10.77CS-170, 10.77CS/200XXL                                                                   | Straightening lifting arm                              | B                 |
| <b>Vermeiren</b>                                                                                           | <b>Spreader Bar</b>                                    | <b>Sling Type</b> |
| Eagle 620, Eagle 625                                                                                       | Spreader Bar                                           | A                 |
| <b>Weiner/Days</b>                                                                                         | <b>Spreader Bar</b>                                    | <b>Sling Type</b> |
| Omnilift G1, Omnilift G2, Omnilift G2A, Omnilift 150, Omnilift 170                                         | Spreader Bar                                           | A                 |
| <b>WIBU</b>                                                                                                | <b>Spreader Bar</b>                                    | <b>Sling Type</b> |
| Atlas, Atlas II, Faun, Solar 175, Ino                                                                      | Sling Bar with 2-, 3-, 4-point hook holder             | A                 |
| Maya, Stellar 160                                                                                          | Straightening lifting arm                              | B, C              |
| <b>WinnCare/Ergolet</b>                                                                                    | <b>Spreader Bar</b>                                    | <b>Sling Type</b> |
| Faun, Faun 2, Flex-Lift 130, Helios, Luna, Pool-Lift, Solar, Winn'Motion 175                               | Sling Bar with 2-, 3-, 4-point hook holder             | A, E              |
| Elev up, Pallas 150/2000/5000, Stellar 160                                                                 | Straightening lifting arm                              | B, C              |

If the hoist you are using is not on this list, we recommend that you contact us to check and confirm the compatibility of our Hoist sling with this lifter.

We confirm conformity with the essential requirements of the Medical Device Regulation (EU) 2017/745 described in Annex I based on the legal requirements of the MDR and the MPBetreibV as well as the requirements of the EN ISO 10535:2021 standard that our body support systems (lift belts) comply with this. Our risk management shows that the proper use of our belts on the listed mobile patient lifts and overhead lifts, in combination with the correct lift Spreader Bar, does not create any additional risks compared to the original system. The combination of our body support systems with the above-mentioned lifts from other manufacturers does not affect the expected performance of the lifters and thus allows us to confirm this compatibility.

## Sling Type A

| Designation                                               | Article-ID                                           |
|-----------------------------------------------------------|------------------------------------------------------|
| SLK Universal Sling Eco, size M/L                         | 5199                                                 |
| SLK Universal Sling, size XXS to 4XL                      | 5221, 5222, 5113, 5114, 5115, 5116, 5117, 5208, 5209 |
| SLK Universal Sling with Headrest, size XXS to XXL        | 5225, 5226, 5119, 5120, 5121, 5122, 5123             |
| SLK Universal Bathroom Sling, size XXS to 4XL             | 5229, 5230, 5124, 5125, 5126, 5127, 5128, 5210, 5211 |
| SLK Universal Bathroom Sling w/ Headrest, size XXS to XXL | 5227, 5228, 5129, 5130, 5131, 5132, 5133             |
| SLK Quick Transfer & Toilet Sling, size XXS to XL         | 5219, 5220, 5134, 5135, 5136, 5137                   |
| SLK Toilet Sling, size S to 4XL                           | 5139, 5140, 5141, 5142, 5143, 5206, 5207             |
| SLK Toilet Sling with Back Reinforcement                  | 5231, 5232, 5233, 5234, 5235                         |
| SLK Hammock Universal Sling, size S to 4XL                | 5144, 5145, 5146, 5147, 5148, 5200, 5201             |
| SLK Hammock Bathroom Sling, size S to 4XL                 | 5149, 5150, 5151, 5152, 5153, 5202, 5203             |
| SLK Hammock Seat Pan Sling, size XXS to 4XL               | 5223, 5224, 5154, 5155, 5156, 5157, 5158, 5204, 5205 |
| SLK Comfort Lying Sling, size S to XXL                    | 5159, 5160, 5161, 5162, 5163                         |
| SLK Comfort Lying Bathroom Sling, size S to XXL           | 5164, 5165, 5166, 5167, 5168                         |
| SLK Back-Fix Sling, size S to XL                          | 5169, 5170, 5171, 5172                               |
| SLK Back-Fix Bathroom Sling, size S to XL                 | 5173, 5174, 5175, 5176                               |
| SLK Maxi Sling, size XXL to 4XL                           | 5177, 5178, 5179                                     |

## Sling Type B

| Designation                     | Article-ID                   |
|---------------------------------|------------------------------|
| SLK Active Sling Eco, size M/L  | 5099                         |
| SLK Active Sling, size S to XXL | 5100, 5101, 5102, 5103, 5104 |

## Sling Type C

| Designation                                             | Article-ID                   |
|---------------------------------------------------------|------------------------------|
| SLK Special Active Sling, size S to L                   | 5105, 5106, 5107             |
| SLK Special Active Sling with Seat Swing, size S to XXL | 5188, 5189, 5190, 5191, 5192 |

## Sling Type D

| Designation             | Article-ID |
|-------------------------|------------|
| SLK 8-Point Lying Sling | 5699       |

## Sling Type E

| Designation       | Article-ID                         |
|-------------------|------------------------------------|
| SLK Walking Sling | 5213, 5214, 5215, 5216, 5217, 5218 |

Waltrop, 07.08.2025  
Ort, Datum



Unterschrift: Frank Keller, Head of Operations